

## AX102641 Cable Management - Angled Management Bar Solution



For more Information  
please call

1-800-793-2954



### General Description:

Angled Management Bar Kit, Black

### Physical Characteristics (Encl-CM)

#### Dimensions

Dimensions:

Height	Depth	Width	Mounting/Style
1.72 inches	4.28 inches	19.62	19 inch Rack Mount

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 06/01/2006

### Notes (Overall)

**Notes:** Elegant installation: With patch cords effectively directed to either side of the rack, the Belden Angled Management Bar Solution allows for long term cable management and attractive cabling installations. Use of the kit prevents patch cord tangling, which degrades the overall installation appearance and inhibits proper MAC's (moves, adds and changes). As the Belden Angled Management Bar Solution can be installed on any flat panel which sits flush with other 19" rack equipment, it allows installations to look uniform. Performance Stability: Since the patch cords are maintained by the patch panel module on one end and the bend radius is optimized by the clip of the Patch Cord Retention Device, the connection stress is completely removed, preventing possible signal failure caused by over-bent patch cords. Best industry labeling scheme with ideal port identification, visible at all times, contrary to flat or angled patch panels, where the termination of patch cords hides the labeling unless great care is taken by the technician to separate thick bundles of patch cords. "V-Shape" angled design Can be used with Belden GigaFlex PS5E, GigaFlex PS6+ and 10GX Patch Cords for front patch cord management, or any patch cord with a diameter between .230 and .280 mil. Can be used with Belden horizontal cables or any horizontal cable with a diameter between .230 and .280 mil.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 02-14-2012

© 2018 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.