

## GDRG

### Multi Loose Tube Cables

#### Outdoor

#### A-DF(ZN)B2Y

Improved Rodent Protection

2015-05-17 v4.0

### Ordering Information

#### Belden European Part Numbers

Fibre Description / count	4	6	8	12	16	24	36
62.5/125-OM1	GDRG104	GDRG106	GDRG108	GDRG112	GDRG116	GDRG124	GDRG136
50/125-OM2 BI	GDRG204	GDRG206	GDRG208	GDRG212	GDRG216	GDRG224	GDRG236
50/125-OM3 BI	GDRGD04	GDRGD06	GDRGD08	GDRGD12	GDRGD16	GDRGD24	GDRGD36
50/125-OM4 BI	GDRGE04	GDRGE06	GDRGE08	GDRGE12	GDRGE16	GDRGE24	GDRGE36
9/125 ITU G.655 C&D	GDRG704	GDRG706	GDRG708	GDRG712	GDRG716	GDRG724	GDRG736
9/125 ITU G.652D & G.657A1 BI	GDRG804	GDRG806	GDRG808	GDRG812	GDRG816	GDRG824	GDRG836
9/125 ITU G.657A2 BI	GDRGF04	GDRGF06	GDRGF08	GDRGF12	GDRGF16	GDRGF24	GDRGF36
9/125 ITU G.657B3 BI	GDRGI04	GDRGI06	GDRGI08	GDRGI12	GDRGI16	GDRGI24	GDRGI36
Std. plywood reel (non-returnable)	Ø 1000 * 530 mm 18 kg						
Std. delivery length	2100 ± 105m						


### Applications

- For **outdoor** use in structured (data) wiring systems such as (**campus backbone**).
- For **outdoor** use in networks for telecom, cable TV and/or broadcast.
- Easy to install in ducts, tunnels and trenches by means of compressed air or pulling wire.
- Suitable for direct burial.

### Features & Benefits

- **Improved rodent protection** provided by waterblocking glassyarns.
- **Predicted lifetime > 30 years.**

## Construction & Dimensions



### Cable Specifications (construction in accordance with IEC 60794)

1. Dielectric central element of glass reinforced plastic (GRP), also as protection against kinks.
2. Jelly filled (non-dripping and silicon-free) loose tubes with primary coated optical fibres ( $\text{Ø } 250 \pm 15 \mu\text{m}$ ).  
Individually colour coded optical fibres: red – green – blue – yellow – violet – pink.
3. The loose tubes are stranded around the central element, if necessary with fillers (PE-natural).  
Colour coding of the loose tubes: 1. red – 2. green – rest white.
4. Jelly filling compound between interstices, and PET foil over cable core.
5. Swellable (for the longitudinal watertightness) glass yarns as strength members.
6. Black UV resistant PE outer jacket.  
Identification: BELDEN OFC – “cable type” – “number x fibre type” + date-, meter- and P/N marking.

### Mechanical Data

No. of fibres	Max. 36
Cable core	6 tubes
Ø Central element (mm)	1.9
Ø Loose tube (mm)	1.9
Ø nom./max. (mm)	11.5 / 11.8
Energy of flame (kJ/m)	3600
Weight (kg/km)	107

## Optical Characteristics

### Characteristics Single-Mode – Matched-Cladded optical fibres according to ITU.

European P/N Coding, Position 5	Fibre-Type	Mode-Field /Cladding Diameter (um)	Wave-length (nm)	Attenuation <sup>B</sup> typical/ max. (dB/km)	Dispersion (ps/(nm·km))	PMD (ps/km)	Cable Cut-off Wave-length (nm)
7	9/125 G.655 C&D	8.4 ± 0.6 125 ± 0.7	1550 1625	0.2 / 0.22 0.21 / 0.24	≤ 4.5 ≤ 7.9	≤ 0.04 <sup>A</sup>	≤ 1260
8	9/125 G.652D & G.657A1 BI OS2	9.2 ± 0.4 125 ± 0.7	1310 1550 1625	0.33 / 0.34 0.18 / 0.19 0.20 / 0.24	≤ 3.2 ≤ 17	≤ 0.06	≤ 1260
F	9/125 G.657A2 BI	8.9 ± 0.4 124.8 ± 0.3	1310 1550 1625	0.34 / 0.35 0.19 / 0.21 0.20 / 0.24	≤ 3.5 ≤ 18	≤ 0.2	≤ 1260
I	9/125 G.657B3 BI	8.8 ± 0.4 125 ± 0.4	1310 1550 1625	0.34 / 0.35 0.19 / 0.21 0.20 / 0.23	≤ 3.5 ≤ 18	≤ 0.06	≤ 1260

Note A- Link design value

Note B- Due to cabling the optical attenuation values can increase with max. 0.05 dB/km

### Characteristics Multi-Mode Graded-Index optical fibres according to IEC 60793

European P/N Coding, Position 5	Fibre-Type	Core/ Cladding Diameter (um)	Wave-length (nm)	Attenuation <sup>C</sup> typical/ max. (dB/km)	Bandwidth (MHz·km)	Ethernet Performance (m)		Num. Apert. (µm)
						1 GBE	10 GBE	
1	62.5/125 OM1	62.5 ± 2.5 125 ± 1	850 1300	2.7 / 3.0 0.7 / 0.8	≥ 200 ≥ 600	220 550	33 300	0.275 ± 0.015
2	50/125 OM2 BI	50 ± 2.5 125 ± 1	850 1300	2.3 / 2.5 0.5 / 0.6	≥ 500 ≥ 500	600 600	83 300	0.20 ± 0.015
D	50/125 OM3 BI	50 ± 2.5 125 ± 1	850 1300	2.3 / 2.5 0.5 / 0.6	≥ 1500 ≥ 500	1000 550	300 300	0.20 ± 0.015
E	50/125 OM4 BI	50 ± 2.5 125 ± 1	850 1300	2.3 / 2.5 0.5 / 0.6	≥ 3500 ≥ 500	1100 550	550 300	0.20 ± 0.015

Note C- Due to cabling the optical attenuation values can increase with max. 0.4 dB/km

## Macro Bending Performance Fibers

Maximum attenuation increase for Bend Insensitive Single Mode fibers in dB depending on turns and radius.

European P/N Coding, Position 5	Fibre-Type	Wave-length (nm)	Turns 100 Radius 30 mm (dB)	Turns 10 Radius 15 mm (dB)	Turn 1 Radius 16 mm (dB)	Turn 1 Radius 10 mm (dB)	Turn 1 Radius 7.5 mm (dB)	Turn 1 Radius 5 mm (dB)
7	9/125 G.655 C & D	1550 1625	0.05 0.05		0.5 0.5			
8	9/125 G.652D & G.657A1 BI OS2	1550 1625	0.03 0.03	0.25 1.0		0.75 1.5		
F	9/125 G.657A2 BI	1550 1625		0.03 0.1		0.1 0.2	0.5 1.0	
I	9/125 G.657B3 BI	1550 1625				0.03 0.1	0.08 0.25	0.15 0.45

Maximum attenuation increase for Bend Insensitive Multi Mode fibers in dB depending on turns and radius.

European P/N Coding, Position 5	Fibre-Type	Wave-length (nm)	Turns 100 Radius 37.5 mm (dB)	Turns 2 Radius 15 mm (dB)	Turns 2 Radius 7.5 mm (dB)
1	62.5/125 OM1	850 1300	0.5 0.5		
2	50/125 OM2 BI	850 1300	0.5 0.5	0.1 0.3	0.2 0.5
D	50/125 OM3 BI	850 1300	0.5 0.5	0.1 0.3	0.2 0.5
E	50/125 OM4 BI	850 1300	0.5 0.5	0.1 0.3	0.2 0.5

## Mechanical, Physical and/or Environmental Characteristics

Description:	Tested according to:	Requirement:	According to Family specification:
Storage Temperature Range	IEC 60794-1-22-F1	-30 to +70 °C	IEC 60794-3-10
Installation Temperature Range		-5 to +50 °C	
Operating Temperature Range		-30 to +70 °C	
Bending Radius Tube (Installation and Operation)		> 25 mm	
Cable Water Blocking	IEC 60794-1-22-F5	Pass	
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	20 x Cable Diam.	IEC 60794-3-10
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E6	20 x Cable Diam.	
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	2000 N	IEC 60794-3-10
Cable Max. Tensile Strength Installation (Short Term)		6000 N	
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3	7.5 kN/m	IEC 60794-3-10
Cable Max. Crush Resistance Installation (Short Term)		15 kN/m	

## Guide to installation and handling

- When laying and installing optical fibre cables it is **vitaly important not to exceed the specified values** set for pulling tension, bending radii and temperature. The installation methods have to be in accordance with the common standards.
- To ease insertion into tubes by means of compressed air or pulling wire, certified lubricants (e.g. paraffin) may be used. The use of soap or similar substances as lubricants is strictly prohibited.
- If a cable needs to be fastened, constrictions > 0.3 mm must be prevented.
- The jelly filling inside the tubes can be removed using a tissue soaked in turpentine.
- It is advisable to cap the cable-ends during storage.

## Options

- Cables for indoor/outdoor use.
- **Non-standard cable constructions**, colours, details and/or additional information regarding specifications are available on request.